

» Features

Download

» Drawing

Print

Q&A

Loading

» Specification Table » Installation Instructions



Features

Mounting | Side mount Side Clearance | 12.7 mm plus 0.8 mm, minus 0 each


Height | 101.6 mm (4")

Loading | 130 pound (60 kgs) class.

Size | 300 mm through 700 mm at 50 mm increment Feature | 32 mm hole pattern, attached release clip with quick disconnect rails for easy drawer removal. Progressive movement. Handed slide member.

Option | Mounting screws.

■ Profile



■ White E Coating

■ Surface Treatment


- Clear Zinc ■ Black Zinc
- Black E. Coating
- Stainless Steel ■ Galvanized Steel

Packaging

- Distribution / 5 pairs per box
- Production

*Box QTY might vary with different length, the info provided here is based on 18" (450 mm)

Drawing



Specification Table

SIZE		SL	TL	Α		C	D				Н
12"	(300mm)	300.0	312.4	224.0				143.1	31.4	268.8	
14"	(350mm)	350.0	361.6	224.0				168.5	31.4	319.6	117.0
16"	(400mm)	400.0	410.8	224.0	320.0			193.9	31.4	370.4	117.0
18"	(450mm)	450.0	460.0	224.0	352.0			219.3	31.4	421.2	117.0
20"	(500mm)	500.0	509.2	224.0	416.0			244.7	31.4	472.0	117.0
22"	(550mm)	550.0	558.4	224.0	352.0	448.0	480.0	270.1	28.4	522.8	117.0
24"	(600mm)	600.0	620.3	224.0	352.0	480.0		295.5	28.4	573.6	117.0
26"	(650mm)	650.0	669.5	224.0	352.0	544.0		320.9	28.4	624.4	117.0
28"	(700mm)	700.0	718.7	224.0	352.0	544.0	608.0	346.3	58.4	645.0	117.0

Installation Instructions

QUICK INSTALLATION GUIDE OF NJ-24007

Loading, Full Extension Slides, 130 pound (60 kgs) loading




READ THE QUICK INSTALLATION GUIDE FIRST BEFORE INSTALLATION

- A. One drawer requires 1 left hand slide, 1 right hand slide and 2 pieces of mounting rails (non-handed)
- B. Recommended screws for fixing #8 pan head screws for drawer fixing; #10 pan head for cabinet fixing. Each side of slide requires at least 6 screws (3 #8 for drawer, 3 #10 for cabinet)

Technical Specifications for drawer or pull-out shelf

- ① Drawer or pulling-out shelf must be at least 13.00 mm narrower than cabinet opening on each side (DIM A)
- 2 Bottom of drawer or pulling-out shelf bottom shall have 6.4 mm or 1/4" minimum clearance from the bottom of Cabinet (DIM B)
 - DIM A
- 3 Mark a center line from the
- bottom of cabinet with the proper height (*H) (DIM C) 4 Mark a center line from the bottom of drawer with the proper height (
- H-6.4 mm + 62 mm) (DIM D)
- * proper height (H) must not be shorter than 26 mm.




Step 1 > Install cabinet member to cabinet


Press the release latch inward to disconnect the mounting rail. (Figure 1)

(Figure 1)


Align the center line of the lower cabinet member to the determined center line (H), and place slide 2 mm backward from cabinet opening.



no screw is bound.




Disconnect the Rail



Step 2 > Install drawer member to drawer

- Align the center line of mounting rail to the determined center line(H-6.4 mm+62 mm), and place the rail 2 mm backward from the drawer front or the pulling-out shelf edge. Shall the silencing cushion is used, place drawer member 5.2 mm backward. (Figure2)
- Fix the drawer member through slots on mounting rail. Leave the screw loose for final adjustment.



Step 3 > Mount drawer on the slides

- Place the mounting rail on the slides, and make sure the rail go under the hook, and the release latch go through square cutout on the opening end of mounting rail. (Figure3)
- Try to lift the drawer up to see if mounting rails are well-engaged with the release latch.

Final Adjustment......

Try to open and close the drawer to see if slides function correctly. If so, secure the screws and install additional screws as necessary.

*This instruction is for reference only. It may vary due to different applications.

